

FEATURES

True Eutectic Solution


- Specially formulated mixture of water, salts and inhibitors.
- Provides stable box temperatures throughout holdover period.
- Injected into plates under a vacuum (30 microns).
- Four temperature ranges available: 0°F (-18°C), -9°F (-23°C), and -18°F (-28°C) for freezer applications and 26°F (-3°C) for refrigerator applications.

Unique Stainless Steel Construction

- Hand polished #304 stainless steel (.062) for clean, aesthetic appearance.
- Easy mount flange system on short side of all plates.
- Internally gusseted steel tubing improves thermal transfer and is high pressure tested to 550 psi.
- Hand welded seams by certified TIG welders.
- Wide variety of sizes and ranges to accommodate various box designs.

Dual Circuit Design

- Permits paralleled operation for engine drive and AC or DC voltage condensing units for redundancy.
- Retrofit crossover assembly for easy conversion to single unit.
- Rapid “pull down” of plate temperature when run with a double pass on one condensing unit.
- Dual set of thermostat sensing wells for accurate temperature control.



Specifications

Plate Selection ⁽¹⁾	12 x 10	16 x 10	20 x 8	20 x 10	16 x 14	24 x 10	24 x 13
Dimensions (in/cm)⁽²⁾							
H1 (Height)	10.0/25.4	14.0/35.6	18.0/45.7	18.0/45.7	14.0/35.6	22.0/55.9	22.0/55.9
H2 (Height) ⁽³⁾	11.5/29.2	15.5/39.4	19.5/49.5	19.5/49.5	15.5/39.4	23.5/59.7	23.5/59.7
W (Width)	10.0/25.4	10.0/25.4	8.0/20.3	10.0/25.4	14.0/35.6	10.0/25.4	13.0/33.0
D (Depth)	26°F and 0°F plates = 3.0/7.6.....-9°F and -18°F plates = 3.38/8.6						
Capacity (BTUs)							
Refrigerator (26°F/-3°C)	1243	1708	1980	2174	2356	2653	3469
Freezer (0°F/-18°C)	1117	1536	1780	1955	2118	2385	3118
Freezer (-9°F/-23°C)	1023	1438	1480	1851	2025	2265	2984
Freezer (-18°F/-28°C)	1058	1486	1531	1914	2095	2342	3086
Weight (lb/kg)	19.0/8.6	26.0/11.8	28.0/12.7	33.0/15.0	34.0/15.5	35.0/15.9	54.0/24.5
Refrigerant Connections ⁽⁴⁾1/2" O.D. x 3/4" L - S.S. Stubs.....						

⁽¹⁾ Plates can be mounted in either horizontal or vertical configurations, with connections either at right, left, up or down. Refrigerant line connections are always located on short dimension of plate.

⁽²⁾ Custom plate sizes on request.

⁽³⁾ Dimension includes two 3/4" (1.9cm) flanges with 1/4" (6.35mm) diameter mounting holes.

⁽⁴⁾ All plates can be prefabricated to customer's requirements, including copper stubs, flare connections and fittings, crossover assemblies and Swagelock™ fittings.

Installation Guidelines for Holdover Plates

When choosing the proper plate sizes, primary consideration should be given to calculated BTU loads as well as box design and usage. Any special requirements must be determined prior to selection and installation.



Holdover plates are available with 26°F (-3°C) eutectic solution for refrigerator box applications, and 0°F (-18°C), -9°F (-23°C) and -18°F (-28°C) solutions for freezer box applications. The freezer plates are identified with 1, 2, or 3 (for the 0, -9 and -18°F plates respectively) V-notches located on the mounting flange at the same end as the refrigerant line connections. The 26°F plates have no notch in the flange. All plates have a serial code and plate temperature inscribed on the back of the mounting flange on the opposite end.

The Grunert line of holdover plates is designed to be installed in any position on a box's interior surface, or as a shelf across the interior space. Each plate has mounting flanges across both short ends (smaller dimension) with 1/4" diameter mounting holes. Secure the plate(s) with the proper fasteners (lag screws, thru-wall connectors, etc.) to support the weight and torsion load from the vessel's movement.

Plates must be mounted with stand-offs to expose the back surface area of the plate to provide proper performance. A minimum of 5/8" (1.6cm) clearance between the box and the back of the plate is recommended.

Expansion valves must be located and fastened properly. Do not install expansion valves with the diaphragm on the bottom. Recommended location of the valve is in the box(es) with the plate. The expansion valve sensing bulbs are to be properly located and secured on the outlet (suction line) of the last plate in series. Recommended location is on a horizontal portion of tubing on the top (between ten and twelve o'clock). If either the expansion valve or its sensing bulb must be located outside of the box, each part must be properly insulated to protect against condensation, as well as to allow accurate temperature sensing of the bulb.

Thermostat sensing bulbs are to be inserted into the sensing wells located on the holdover plate. Two sets of wells are located on two sides of each plate. Once a plate has been positioned in a box, the well(s) that are located on the side (vertical surface) should be used for the most accurate sensing of plate temperature.



26°F REFRIGERATOR PLATE	VOLUME IN CUBIC FEET*			
	INSULATION**			
	6"	4"	3"	2"
5200				14
5000				13
4800				12
4600				11
4400				10
4200				9
4000				8
3800				7
3600				6
3400				5
3200				4
3000				3
2800				2
2600				1
2400				
2200				
2000				
1800				
1600				
1400				
1200				
1000				

0°F FREEZER PLATE	VOLUME IN CUBIC FEET*			
	INSULATION**			
	6"	4"	3"	2"
5200	16	11	8	5
5000	14	10	7	
4800	14	10	7	
4600	12	8	6	4
4400	12	8	6	4
4200	10	6	5	3
4000	10	6	5	3
3800	8	6	4	
3600	8	6	4	
3400	6	4	3	2
3200	6	4	3	2
3000	4	3	2	
2800	4	3	2	
2600	3	2	1	
2400	3	2	1	
2200	2	2	1	
2000	2	2	1	
1800	1	1	1	
1600	1	1	1	
1400				
1200				
1000				

-9°F FREEZER PLATE	VOLUME IN CUBIC FEET*				BTU LEAK IN 24 HOURS
	INSULATION**				
	6"	4"	3"	2"	
5200	10				9600
5000	14				9400
4800					9200
4600	12				9000
4400		8			8800
4200	10				8600
4000		6			8400
3800	8				8200
3600					8000
3400	6	4			7800
3200					7600
3000		3		20	7400
2800	4				7200
2600				18	7000
2400		2			6800
2200	2				6600
2000				16	6400
1800		1			6200
1600	1			14	6000
1400				20	5800
1200				18	5600
1000				16	5400

-18°F FREEZER PLATE	VOLUME IN CUBIC FEET*				BTU LEAK IN 24 HOURS
	INSULATION**				
	6"	4"	3"	2"	
5200	12	8			9600
5000					9400
4800	10				9200
4600					9000
4400	8	6			8800
4200					8600
4000					8400
3800	6			20	8200
3600		4			8000
3400				18	7800
3200	4	3			7600
3000					7400
2800	3			16	7200
2600		2			7000
2400	2				6800
2200				14	6600
2000		1			6400
1800	1	1		12	6200
1600				16	6000
1400				10	5800
1200				14	5600
1000					5400

③ EXAMPLE CIRCLED: A 0° freezer box with inside dimensions of 24" height, 12" depth and 18" width has an internal volume of 5184 cubic inches (24x12x18). Divide the 5184 cubic inches by 1728 (one cubic foot) to get three cubic feet. With 4" of insulation, a 2700BTU leak is found from the chart. Referring to the 0° Freezer Capacity (BTUs) row on the front of this sheet, two 16x10 plates (3072BTUs) or one 24x13 plate (3118BTUs) may be used.

- * TO CONVERT CUBIC METERS TO CUBIC FEET, MULTIPLY BY 35.31
- ** CHART IS DESIGNED USING POLY FOAM WITH A TWO POUND DENSITY RATING

In the interest of product improvement, Taylor Made Environmental's specifications and design as outlined herein are subject to change without prior notice.



Taylor Made ENVIRONMENTAL™

Sold and Serviced By:

Taylor Made Environmental, Inc.

P.O. Box 15299 • Richmond, VA USA 23227-0699 • 804-746-7248 • Fax: 804-746-7248 • sales@tmenviro-va.com • www.cruisair.com
 2000 N. Andrews Ave. Ext. • Pompano Beach, FL USA 33069-1497 • 954-973-2477 • Fax: 954-979-4414 • sales@tmenviro-fl.com • www.marineair.com
 Fleet Industrial Estate • 26 Willis Way • Poole, Dorset • England BH15 3SCU • 44 (0) 870 3306101 • Fax: 44 (0) 870 3306102 • sales@tmenviro-eu.com

©Taylor★Made is a registered trademark of Nelson A. Taylor Co., Inc.; The Marine Air Systems logo is a registered trademark and the Taylor Made Environmental logo is a registered trademark of Taylor Made Environmental, Inc.

Taylor Made Environmental, Inc. 1/01

A Member of
THE TAYLOR MADE GROUP.